# TECHNICAL DATA SHEET



Value

0.97

0.97

20:1

Gel

300 cP

220 cP

**Transparent** 

204 °C / 399 °F

-55 °C / -67 °F

38 °C / 100 °F

3 - 7 mm

24 mths

Addition

> 7 days

**Test Method** 

BS ISO 2781

BS ISO 2781

**Brookfield** 

**Brookfield** 

## **QGel 313 Custom Silicone Gel**

**Property** 

Cure Type

Density A

Density B

Rheology

Viscosity A

Viscosity B

Color

**Cured Product** 

Max Working Temp

Min Working Temp

Penetration (19.5g Cone

**Uncured Product** 

Gel Time at 25°C/77°F

Mix Ratio By Weight

Description
QGels are addition-cure clear, soft, moderately cross-linked
silicone polymer. Silicone gels provide protection from moisture,
vibration, thermal, or mechanical shock.

### **Key Features**

Description

- 20:1 mix ratio
- Greater than 7-day room temperature work life
- Dispensing equipment not necessary
- Heat cure required

#### **Use and Cure Information**

#### **Important**

In order to achieve optimum performance, the same lot number of the A and B components should be used. Mixed lots may not obtain the performance criteria listed on the TDS or Certificate of

The "A" part of QGels contain the platinum catalyst; great care should be taken when using automated dispensing equipment to not cross-contaminate systems.

components are mixed, the curing process begins. The gel time of the mixed material is listed under the typical properties. Fast

Weight) mm Both the "A" and "B" parts should be well stirred to ensure the Storage material is uniform. QGels should be mixed by weight. Once the Max Storage Temperature Shelf Life

dispensing equipment. In order to achieve optimum performance, the same "A" and "B" side lot numbers should be used.

	La la la Laboration de la constantia del constantia de la	AP 4 1 2 2 2 2 3 4 1 1 1 1 1 1 2 2 3 4 4 4 4 4 4 4 4 4 4 4 4 4 4 4 4 4		1		
CHIRING GE	ie enaliia na i	dispensed utilizing	automatec	ı mıv and		
curing gc	is silicula be i		automatec	i iiiix aiiu		
		la audau ta aabia.				

Air trapped during mixing should be removed to eliminate voids in the cured product. Vacuum de-airing may be necessary to completely remove all entrapped air bubbles. To ensure proper de-airing, subject the mixed material to 29 inches of mercury.

#### Storage and Shelf-life

This product is best when used within 24 months from the date of manufacture, See product label and/or the CoA for specific "use by date". Product should be stored in its original, unopened container in an environment that does not exceed 38C (100F)

Storage beyond the date specified on the label does not necessarily mean that the product is no longer usable. In this case, the properties required for the intended use should be checked for quality assurance reasons.

Revision Date 10 Nov 2021

Revision No 5

**Download Date** 25 Apr 2024

CHT make reasonable efforts to ensure that information set out in the technical data sheet is complete, accurate, and up-to-date. CHT do not, however, make any representations, warranties or guarantees (whether express or implied) that information set out in the technical data sheet is complete, accurate, or up-to-date or that the product will be suitable for your requirements. You should carry out your own testing to determine the applicability of such information and whether the product will be suitable. CHT reserve the right to modify the technical data sheet at any time. The CHT technical service department is available to offer further information and advice and should it be needed to look at modifying current products or custom formulate a new one to meet your specific requirements. Please contact the technical service department.