

## TufGel 3350 Two-part, Self-Bonding High Strength Silicone Gel

### Description

This is one of a family of soft, adherent, silicone elastomeric gels designed for the encapsulation and protection of electronic components. It is a low viscosity, 2-component system that is readily mixed in a 1:1 ratio. It is used to provide protection from vibration, thermal or mechanical shock and protection from water and many environmental contaminants. It has excellent dielectric properties.

### Key Features

- Low modulus minimizes stress on parts and components
- Fast room temperature cure
- Potted or encapsulated assemblies can be repaired with modest effort
- Primerless chemical adhesion at room temperature to many substrates

### Use and Cure Information

#### IMPORTANT:

In order to achieve optimum performance, the same lot number of the A and B components should be used. Mixed lots may not obtain the performance criteria listed on the TDS or Certificate of Analysis.

The 'A' part of the product contains the platinum catalyst; great care should be taken when using automatic dispensing equipment. Please ensure that it is not contaminated by residual hydride containing rubber (Part B) in the dispensing equipment, as curing will result. If in doubt, it is advised to thoroughly purge the equipment with a suitable hydrocarbon solvent or silicone fluid.

### Mixing

Both the 'A' and 'B' parts should be well stirred to ensure the material is uniform and any settled fillers have been remixed.

Place the required amount of 'A' and 'B' parts by weight at the mix ratio shown opposite, in a clean plastic or metal container of approximately 3 times their volume, and mix until the colour of the mixture is uniform. For best results, we recommend degassing. Degas by intermittent evacuation, the larger volume of the mixing vessel helps prevent overflow during this operation. In the case of automatic dispensing with static mixing head, the two components should be degassed before processing. Recommended vacuum conditions are 30-50 mbar intermittently over 5-10 minutes. Cast the mixture either by gravity or pressure injection.

### Inhibition of Cure

Great care must be taken when handling and mixing all addition cured silicone elastomer systems, ensuring that all the mixing tools (vessels and spatulas) are clean and constructed in materials which do not interfere with the curing mechanism. The cure of the rubber can be inhibited by the presence of compounds of nitrogen, sulphur, phosphorus and arsenic; organotin catalysts and PVC stabilizers; epoxy resin catalysts and even contact with materials containing certain of these substances e.g. moulding clays, sulphur vulcanised rubbers, condensation cure silicone rubbers, onion and garlic.

### Curing Conditions

The data offers a guide to the rate of cure at various temperatures, mixing of the components at temperatures between 15 and 25°C is recommended to ensure adequate pot life for degassing and handling. The pot life can be extended to several hours by chilling the components before mixing.

It is important to check the compatibility in preliminary tests if unknown substrates are used.

### Health & Safety

Safety Data Sheets available on request.

### Packaging

CHT Gels are available in a variety of packaging including bulk containers. Please contact our sales department for more information.

Revision Date 17 Oct 2021

| Property                | Test Method    | Value  |
|-------------------------|----------------|--|
| <b>Uncured Product</b>  |                |  |
| Color A                 |                | Transparent yellow                           |
| Color B                 |                | Transparent and colorless                    |
| Cure Profile            |                | 30 mins at 70°C, 60 mins at room temperature |
| Cure Type               |                | Addition                                     |
| Gel Time at 25°C/77°F   |                | 6.5 min                                      |
| Mix Ratio By Weight     |                | 1:1  |
| Rheology                |                | Liquid, Newtonian                            |
| Self Bonding            |                | Yes  |
| Specific Gravity A      |                | 0.97   |
| Specific Gravity B      |                | 0.97   |
| Viscosity A             | Brookfield     | 275 cP                                       |
| Viscosity B             | Brookfield     | 550 cP                                       |
| Viscosity Mixed         | Brookfield     | 390 cP                                       |
| <b>Cured Product</b>    |                |  |
| Color                   |                | Transparent yellow                           |
| Hardness Shore 00       | ASTM D 2240-95 | 45 - 60                                      |
| Max Working Temp        |                | 204 °C / 399 °F                              |
| Min Working Temp        |                | -55 °C / -67 °F                              |
| <b>Storage</b>          |                |  |
| Max Storage Temperature |                | 38 °C / 100 °F                               |
| Shelf Life              |                | 24 mths                                      |

The content set out in the technical data sheet does not contain information upon which you should rely. It is provided for general information purposes only and does not constitute a product specification. You must obtain professional or specialist advice before taking any action based on the information provided in the technical data sheet.

CHT make reasonable efforts to ensure that information set out in the technical data sheet is complete, accurate, and up-to-date. CHT do not, however, make any representations, warranties or guarantees (whether express or implied) that information set out in the technical data sheet is complete, accurate, or up-to-date or that the product will be suitable for your requirements. You should carry out your own testing to determine the applicability of such information and whether the product will be suitable. CHT reserve the right to modify the technical data sheet at any time.

The CHT technical service department is available to offer further information and advice and should it be needed to look at modifying current products or custom formulate a new one to meet your specific requirements. Please contact the technical service department.

**CHT Germany GmbH:** Postfach 12 80, 72002 Tübingen, Bismarckstraße 102, 72072 Tübingen, Germany  
Telephone: 07071/154-0, Fax: 07071/154-290, Email: info@cht.com, Homepage: www.cht.com / www.cht-silicones.com

Revision No 8  
Download Date 29 Nov 2021

---

The content set out in the technical data sheet does not contain information upon which you should rely. It is provided for general information purposes only and does not constitute a product specification. You must obtain professional or specialist advice before taking any action based on the information provided in the technical data sheet.

CHT make reasonable efforts to ensure that information set out in the technical data sheet is complete, accurate, and up-to-date. CHT do not, however, make any representations, warranties or guarantees (whether express or implied) that information set out in the technical data sheet is complete, accurate, or up-to-date or that the product will be suitable for your requirements. You should carry out your own testing to determine the applicability of such information and whether the product will be suitable. CHT reserve the right to modify the technical data sheet at any time.

The CHT technical service department is available to offer further information and advice and should it be needed to look at modifying current products or custom formulate a new one to meet your specific requirements. Please contact the technical service department.

**CHT Germany GmbH:** Postfach 12 80, 72002 Tübingen, Bismarckstraße 102, 72072 Tübingen, Germany  
Telephone: 07071/154-0, Fax: 07071/154-290, Email: [info@cht.com](mailto:info@cht.com), Homepage: [www.cht.com](http://www.cht.com) / [www.cht-silicones.com](http://www.cht-silicones.com)