

QM Pt Accelerator Addition cure curing accelerator

Description

This can be used with two-component, room temperature, addition cure, silicone materials to reduce the de-mold time. When added at 1% to the silicone base, it will reduce the de-mold time by roughly one half. The work time will also be significantly reduced.

This product can also be used as a surface treatment to prevent inhibition.

Key Features

- Reduces de-mold time
- Low Viscosity
- Casting resin resistance
- Inhibition resistance

Use and Cure Information

The applications for this are numerous and varied. All application methods and recommended levels must be considered on an individual basis. Contact the CHT USA customer service team or your sales representative for details.

Health & Safety

Safety Data Sheets available on request.

Property

Uncured Product

Color

Cure Type

Rheology

Specific Gravity

Viscosity

Test Method

Brookfield

Value

Clear

Addition

Liquid

0.97

2,200 cP

Storage

Max Storage

Temperature

Shelf Life

38 °C / 100 °F

24 mths

Revision Date 14 Oct 2021

Revision No 4

Download Date 19 Apr 2024

The content set out in the technical data sheet does not contain information upon which you should rely. It is provided for general information purposes only and does not constitute a product specification. You must obtain professional or specialist advice before taking any action based on the information provided in the technical data sheet. CHT make reasonable efforts to ensure that information set out in the technical data sheet is complete, accurate, and up-to-date. CHT do not, however, make any representations, warranties or guarantees (whether express or implied) that information set out in the technical data sheet is complete, accurate, or up-to-date or that the product will be suitable for your requirements. You should carry out your own testing to determine the applicability of such information and whether the product will be suitable. CHT reserve the right to modify the technical data sheet at any time. The CHT technical service department is available to offer further information and advice and should it be needed to look at modifying current products or custom formulate a new one to meet your specific requirements. Please contact the technical service department.

CHT Germany GmbH: Postfach 12 80, 72002 Tübingen, Bismarckstraße 102, 72072 Tübingen, Germany
Telephone: 07071/154-0, Fax: 07071/154-290, Email: info@cht.com, Homepage: www.cht.com / www.cht-silicones.com