

## MM830 2 part moulding compound

### Description

This is a two-component low tear room temperature condensation cure silicone system. The cured rubber is suitable for the mould making of patterns with fine details, where some dimensional stability is required. Low tear silicone moulding rubbers are cost effective for the production of moulds only requiring a few impressions. They find uses in the reproduction of plane surface objects

### Key Features

- Easy demoulding
- Easily degassed
- Low viscosity
- Fine detail pick up

### Application

reproduction of plane surface models

### Use and Cure Information

The curing process starts as soon as the catalyst is added. Under normal conditions of temperature and humidity typical curing characteristics are described below. If the product is to be used in contact with aggressive chemicals, such as high styrene polyester resins or epoxies, it is recommended that the rubber be allowed to cure for 48 hours before use.

Pour the catalysed rubber into the mould from one point, ensuring air is not entrapped. Allow the rubber to cure before removing from the mould. To allow the rubber to achieve its maximum physical properties and chemical resistance leave the partially cured rubber to age at room temperature for at least a further 12 hours.

### How to Use

Charge the base rubber into a clean plastic or metal container, approximately 3-4 times its volume.

Add standard catalyst in the proportion of 5 parts by weight of catalyst to 100 parts by weight of the rubber base. Mix thoroughly, slowly at first to avoid splashing and taking care to avoid excessive air entrapment. After catalysation any entrapped air may be removed by intermittent evacuation for several minutes. The use of a sufficiently large container permits degassing without overflow.

### Catalysts

Use the following catalysts:

MM Product	Feature	Colour	Mixing ratio	Demould time [h]	Pot life [mins]
<b>Low tear catalyst (MM800 series)</b>					
CAT L6W NT	Standard cure, leather reproduction	Clear	20:1	<24	>45
CAT VEI INCOLORE NT	Fast cure, shoe sole moulds	Clear	20:1	2	15
<b>Additive</b>					
MM CAT W*	Booster to accelerate cure	Clear	100:1	1-2	15
MM TA2	Thixotropic agent	Clear	100:2	N/A	N/A

### Health & Safety

#### Health and Safety

Safety Data Sheets available on request.

#### Packaging

CHT Moulding Rubbers are available in a variety packaging including bulk containers. Please contact our sales department for more information.

Revision Date 18 Jun 2025  
Revision No 4  
Download Date 09 May 2026

### Property

#### Uncured Product

Cure Profile		<b>23°C and 50% humidity</b>
Cure Type		<b>Condensation</b>
De-mould Time / Full Cure at 23°C/73°F: hrs		<b>24 hr hrs</b>
Mix Ratio By Weight		<b>20:1</b>
Pot Life mins at 23°C/73°F		<b>60 mins</b>
Rheology		<b>Liquid</b>
Viscosity Mixed	Brookfield	<b>10800 cP</b>

#### Cured Product

<b>7 days at 23+/-2°C and 50+/-5% humidity</b>		
Color		<b>White</b>
Density	BS ISO 2781	<b>1.11 g/cm3</b>
Elongation at Break	ISO 37	<b>200 %</b>
Hardness Shore A	ASTM D 2240-95	<b>27</b>
Linear Shrinkage (%)		<b>0.5 %</b>
Max Working Temp		<b>200 °C / 392 °F</b>
Min Working Temp		<b>-50 °C / -58 °F</b>
Tear Resistance (N/mm)	BS ISO 34-1	<b>2 N/mm / 11 ppi</b>
Tensile Strength	ISO 37	<b>1.5 N/mm2 / 218 psi</b>

#### Storage

Max Storage Temperature	<b>40 °C / 104 °F</b>
Shelf Life	<b>12 mths</b>

The content set out in the technical data sheet does not contain information upon which you should rely. It is provided for general information purposes only and does not constitute a product specification. You must obtain professional or specialist advice before taking any action based on the information provided in the technical data sheet.

CHT make reasonable efforts to ensure that information set out in the technical data sheet is complete, accurate, and up-to-date. CHT do not, however, make any representations, warranties or guarantees (whether express or implied) that information set out in the technical data sheet is complete, accurate, or up-to-date or that the product will be suitable for your requirements. You should carry out your own testing to determine the applicability of such information and whether the product will be suitable. CHT reserve the right to modify the technical data sheet at any time. The CHT technical service department is available to offer further information and advice and should it be needed to look at modifying current products or custom formulate a new one to meet your specific requirements. Please contact the technical service department.

CHT Germany GmbH: Postfach 12 80, 72002 Tübingen, Bismarckstraße 102, 72072 Tübingen, Germany  
Telephone: 07071/154-0, Fax: 07071/154-290, Email: info@cht.com, Homepage: www.cht.com / www.cht-silicones.com