

## QM 262 2 Part Mold Making Silicone

| Description   | Property   | Test Method   | Value  |
|---|--|---|--|
| <p>This is a pourable 2-part addition cure silicone elastomer system. After mixing parts 'A' and 'B' in the correct proportions, the system will cure at ambient temperatures within 24 hours, but the rate of cure can be accelerated by heat. The cured rubber exhibits excellent physical and electrical properties.</p> <p><b>Key Features</b></p> <ul style="list-style-type: none"> <li>• Low viscosity</li> <li>• Casting resin resistance</li> <li>• Fast demold time</li> <li>• FDA CFR 177.2600 compliant</li> </ul> <p><b>Key Applications</b></p> <ul style="list-style-type: none"> <li>• Molds for polyester, epoxy resin casting</li> <li>• Candy and other food molds</li> <li>• Picture frames and furniture replication</li> <li>• Prototyping</li> </ul> <p><b>Application</b></p> <p>Addition cure mold making silicone for rapid prototyping, roller manufacturing and architectural reproduction.</p> <p><b>Use and Cure Information</b></p> <p><b>IMPORTANT:</b></p> <p>The 'A' part of product contains the platinum catalyst; great care should be taken when using automatic dispensing equipment. Please ensure that it is not contaminated by residual hydride containing rubber in the dispensing equipment, as curing will result. If in doubt, it's advised to thoroughly purge the equipment with a suitable hydrocarbon solvent or silicone fluid.</p> <p><b>Mixing</b></p> <p>Both the 'A' and 'B' parts should be well stirred to ensure the material is uniform and any settlement of the fillers have been remixed. Place the required amount of 'A' and 'B' parts by weight at the mix ratio shown opposite, in a clean plastic or metal container of approximately 3 times their volume, and mix until the colour of the mixture is uniform. For best results, we recommend degassing. Degas by intermittent evacuation, the larger volume of the mixing vessel helps prevent overflow during this operation. In case of automatic dispensing with static mixing head, the two components should be degassed before processing. Recommended vacuum conditions are 30-50 mbar intermittently over 5-10 minutes. Cast the mixture either by gravity or pressure injection. In order to achieve optimum performance, the same "A" and "B" side lot number should be used.</p> <p><b>Inhibition of Cure</b></p> <p>Great care must be taken when handling and mixing all addition cured silicone elastomer systems, ensuring that all the mixing tools (vessels and spatulas) are clean and constructed in materials which do not interfere with the curing mechanism. The cure of the rubber can be inhibited by the presence of compounds of nitrogen, sulphur, phosphorus and arsenic; organotin catalysts and PVC stabilizers; epoxy resin catalysts and even contact with materials containing certain of these substances e.g. moulding clays, sulphur vulcanised rubbers, condensation cure silicone rubbers, onion and garlic.</p> <p><b>Curing Conditions</b></p> <p>The data offers a guide to the rate of cure at various temperatures, mixing of the components at temperatures between 15 and 25°C is recommended to ensure adequate pot life for degassing and handling. The pot life can be extended to several hours by chilling the components before mixing.</p> <p><b>Health &amp; Safety</b></p> <p>Safety Data Sheets available on request.</p> <p><b>Packaging</b></p> <p>CHT Moulding Rubbers are available in a variety packaging including bulk containers. Please contact our sales department for more information.</p> | <p><b>Uncured Product</b></p> <p>Color A</p> <p>Color B</p> <p>Cure Type</p> <p>De-mould Time / Full Cure at 23°C/73°F</p> <p>Density A</p> <p>Density B</p> <p>Mix Ratio By Weight</p> <p>Pot Life mins at 23°C/73°F</p> <p>Viscosity A</p> <p>Viscosity B</p> <p>Viscosity Mixed</p> |   | <p><b>Beige</b></p> <p><b>Blue</b></p> <p><b>Addition</b></p> <p><b>8 - 12 hrs</b></p> <p><b>1.26</b></p> <p><b>1.02</b></p> <p><b>10:1</b></p> <p><b>60 mins</b></p> <p><b>45,000 cP</b></p> <p><b>2,000 cP</b></p> <p><b>35,000 cP</b></p>                 |
|   |  | <p><b>Cured Product</b></p> <p><b>150 C for 30 mins</b></p> <p>Color</p> <p>Density</p> <p>Elongation at Break</p> <p>FDA Tested</p> <p>Hardness Shore A</p> <p>Linear Shrinkage (%)</p> <p>Max Working Temp</p> <p>Min Working Temp</p> <p>Tear Resistance (N/mm)</p> <p>Tensile Strength</p> <p><b>Storage</b></p> <p>Max Storage Temperature</p> <p>Shelf Life</p> | <p>BS ISO 2781</p> <p>BS ISO 2781</p> <p></p> <p>Brookfield</p> <p>Brookfield</p> <p>Brookfield</p> <p></p> <p>BS ISO 2781</p> <p>ISO 37</p> <p>CFR (21] 177.2600</p> <p>ASTM D 2240-95</p> <p></p> <p>BS ISO 34-1</p> <p>ISO 37</p> <p></p> <p></p> <p></p> |

---

The content set out in the technical data sheet does not contain information upon which you should rely. It is provided for general information purposes only and does not constitute a product specification. You must obtain professional or specialist advice before taking any action based on the information provided in the technical data sheet.

CHT make reasonable efforts to ensure that information set out in the technical data sheet is complete, accurate, and up-to-date. CHT do not, however, make any representations, warranties or guarantees (whether express or implied) that information set out in the technical data sheet is complete, accurate, or up-to-date or that the product will be suitable for your requirements. You should carry out your own testing to determine the applicability of such information and whether the product will be suitable. CHT reserve the right to modify the technical data sheet at any time. The CHT technical service department is available to offer further information and advice and should it be needed to look at modifying current products or custom formulate a new one to meet your specific requirements. Please contact the technical service department.

**CHT Germany GmbH:** Postfach 12 80, 72002 Tübingen, Bismarckstraße 102, 72072 Tübingen, Germany  
Telephone: 07071/154-0, Fax: 07071/154-290, Email: [info@cht.com](mailto:info@cht.com), Homepage: [www.cht.com](http://www.cht.com) / [www.cht-silicones.com](http://www.cht-silicones.com)