

## QVB 720 2 Part Molding Silicone for Reusable Vacuum Bags

Description	Property	Test Method	Value	
<p>This is a pourable 2-part addition cure silicone elastomer system. After mixing parts 'A' and 'B' in the correct proportions, the system will cure at ambient temperatures within 24 hours, but the rate of cure can be accelerated by heat. The cured rubber exhibits excellent physical and electrical properties.</p> <p><b>Key Features</b></p> <ul style="list-style-type: none"> <li>• Transparent purple in thin cured sections which enables layer thickness evaluation</li> <li>• Fast gel time</li> <li>• Excellent tear and elongation properties</li> <li>• Flowable, self-leveling and mildly thixotropic for vertical surfaces</li> </ul> <p><b>Key Applications</b></p> <ul style="list-style-type: none"> <li>• Closed molding</li> <li>• Composite part manufacturing</li> <li>• Resin infusion/pre-preg</li> <li>•</li> </ul> <p><b>Application</b></p> <p>QVB 720 is a silicone molding rubber for producing reusable vacuum bags. This formulation can also be used as a moldmaking material if a fast cure is required.</p> <p><b>Note:</b></p> <p>An equivalent final formulation is also available as a 1:10 mix ratio (by weight or volume only) if fixed-ratio dispensing equipment is desired. Refer to QVB 701 Technical Data Sheet.</p> <p><b>Use and Cure Information</b></p> <p><b>IMPORTANT:</b></p> <p>The 'A' part of product contains the platinum catalyst; great care should be taken when using automatic dispensing equipment. Please ensure that it is not contaminated by residual hydride containing rubber in the dispensing equipment, as curing will result. If in doubt, it's advised to thoroughly purge the equipment with a suitable hydrocarbon solvent or silicone fluid.</p> <p><b>Mixing</b></p> <p>Both the 'A' and 'B' parts should be well stirred to ensure the material is uniform and any settlement of the fillers have been remixed. Place the required amount of 'A' and 'B' parts by weight at the mix ratio shown opposite, in a clean plastic or metal container of approximately 3 times their volume, and mix until the colour of the mixture is uniform. For best results, we recommend degassing. Degas by intermittent evacuation, the larger volume of the mixing vessel helps prevent overflow during this operation. In case of automatic dispensing with static mixing head, the two components should be degassed before processing. Recommended vacuum conditions are 30-50 mbar intermittently over 5-10 minutes. Cast the mixture either by gravity or pressure injection. In order to achieve optimum performance, the same "A" and "B" side lot number should be used.</p> <p><b>Inhibition of Cure</b></p> <p>Great care must be taken when handling and mixing all addition cured silicone elastomer systems, ensuring that all the mixing tools (vessels and spatulas) are clean and constructed in materials which do not interfere with the curing mechanism. The cure of the rubber can be inhibited by the presence of compounds of nitrogen, sulphur, phosphorus and arsenic; organotin catalysts and PVC stabilizers; epoxy resin catalysts and even contact with materials containing certain of these substances e.g. moulding clays, sulphur vulcanised rubbers, condensation cure silicone rubbers, onion and garlic.</p> <p><b>Curing Conditions</b></p> <p>The data offers a guide to the rate of cure at various temperatures, mixing of the components at temperatures between 15 and 25°C is recommended to ensure adequate pot life for degassing and handling. The pot life can be extended to several hours by chilling the components before mixing.</p> <p><b>Health &amp; Safety</b></p> <p>Safety Data Sheets available on request.</p> <p><b>Packaging</b></p> <p>CHT Moulding Rubbers are available in a variety packaging including bulk containers. Please contact our sales department for more information.</p>	<p><b>Uncured Product</b></p> <p>Color A Color B Cure Type Density A Density B Gel Time at 25°C/77°F Mix Ratio By Weight Viscosity A Viscosity B</p>	<p>BS ISO 2781 BS ISO 2781  Brookfield Brookfield</p>	<p><b>Translucent white</b> <b>Translucent purple</b> <b>Addition</b> <b>1.07</b> <b>1.07</b> <b>8-13 mins</b> <b>1:1</b> <b>35,000 cP</b> <b>35,000 cP</b></p>	
		<p><b>Cured Product</b></p> <p>Color Density Elongation at Break Hardness Shore A Linear Shrinkage (%) Tear Resistance (N/mm) Tensile Strength</p>	<p>BS ISO 2781 ISO 37 ASTM D 2240-95  BS ISO 34-1 ISO 37</p>	<p><b>Translucent purple</b> <b>1.07 g/cm<sup>3</sup></b> <b>800 %</b> <b>28</b> <b>&lt; 0.1% %</b> <b>10.50 N/mm / 60 ppi</b> <b>4.826 N/mm<sup>2</sup> / 700 psi</b></p>
		<p><b>Storage</b></p> <p>Max Storage Temperature Shelf Life</p>		<p><b>38 °C / 100 °F</b> <b>24 mths</b></p>

Revision Date 20 Oct 2021  
Revision No 3  
Download Date 16 May 2022

The content set out in the technical data sheet does not contain information upon which you should rely. It is provided for general information purposes only and does not constitute a product specification. You must obtain professional or specialist advice before taking any action based on the information provided in the technical data sheet. CHT make reasonable efforts to ensure that information set out in the technical data sheet is complete, accurate, and up-to-date. CHT do not, however, make any representations, warranties or guarantees (whether express or implied) that information set out in the technical data sheet is complete, accurate, or up-to-date or that the product will be suitable for your requirements. You should carry out your own testing to determine the applicability of such information and whether the product will be suitable. CHT reserve the right to modify the technical data sheet at any time. The CHT technical service department is available to offer further information and advice and should it be needed to look at modifying current products or custom formulate a new one to meet your specific requirements. Please contact the technical service department.  
**CHT Germany GmbH:** Postfach 12 80, 72002 Tübingen, Bismarckstraße 102, 72072 Tübingen, Germany  
Telephone: 07071/154-0, Fax: 07071/154-290, Email: info@cht.com, Homepage: www.cht.com / www.cht-silicones.com

---

The content set out in the technical data sheet does not contain information upon which you should rely. It is provided for general information purposes only and does not constitute a product specification. You must obtain professional or specialist advice before taking any action based on the information provided in the technical data sheet.

CHT make reasonable efforts to ensure that information set out in the technical data sheet is complete, accurate, and up-to-date. CHT do not, however, make any representations, warranties or guarantees (whether express or implied) that information set out in the technical data sheet is complete, accurate, or up-to-date or that the product will be suitable for your requirements. You should carry out your own testing to determine the applicability of such information and whether the product will be suitable. CHT reserve the right to modify the technical data sheet at any time. The CHT technical service department is available to offer further information and advice and should it be needed to look at modifying current products or custom formulate a new one to meet your specific requirements. Please contact the technical service department.

**CHT Germany GmbH:** Postfach 12 80, 72002 Tübingen, Bismarckstraße 102, 72072 Tübingen, Germany  
Telephone: 07071/154-0, Fax: 07071/154-290, Email: [info@cht.com](mailto:info@cht.com), Homepage: [www.cht.com](http://www.cht.com) / [www.cht-silicones.com](http://www.cht-silicones.com)